

**MICRO SWITCH**  
a Honeywell Division

FED. MFG. CODE 91929

# SWITCH-BASIC

CATALOG LISTING

V7-1A27D8-207

CW-B0470

CATALOG LISTING

V7-1A27D8-207

REPLACES

RELEASE NO. PR-19258

**M**

ISSUE  
2

CHECK

REVISIONS  
A CO 76440  
JWB  
30 NOV 93

CHECK



4 JUN 91

D C S

CHECK

J A L 24 MAY 91


DDM/CAD  
DRAWN




ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE— — — 86 GRAMS MAX	CONTACT ARRANGEMENT S P N O	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE— — — 9 GRAMS MIN	L162 5A 125, <u>250</u> , 277 VAC 1/10HP <u>250</u> VAC 	ONE PLACE (.0)	±.030
DIFFERENTIAL TRAVEL— — — .025 MAX		TWO PLACE (.00)	±.015
OVERTRAVEL — — — — .064 MIN		THREE PLACE (.000)	±.005
RELEASE TRAVEL— — — — .016 MIN		ANGLES	±
		WEIGHT	



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-1A27D8-207](#)