



- NOTES
- 1 - UNIT INCLUDES "HM" TYPE BASIC SWITCH
  - 2 - TERMINALS ARE PLATED FOR SOLDERING
  - 3 FOR PANEL SEAL TO BE EFFECTIVE MOUNTING HOLE IN PANEL SHOULD NOT EXCEED Ø.500
  - 4 HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET PER MIL-PRF-8805

ANSI Y14.5M-1982 APPLIES		THIRD ANGLE PROJECTION	
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		SCALE FULL	
CHARACTERISTICS	ELECTRICAL DATA	DO NOT SCALE PRINT	
	CONTACT ARRANGEMENT SPDT	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
	28 VOLTS DC RATING	ONE PLACE	(.0) ±.030
	INDUCTIVE ----- SEA LEVEL - 1/4 AMP	TWO PLACE	(.00) ±.015
	70,000 FT --- 1/4 AMP	THREE PLACE	(.000) ±.005
	RESISTIVE ----- SEA LEVEL - 1/2 AMP	ANGLES	±
	70,000 FT --- 1/2 AMP	WEIGHT	.06 LB APPROX

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[232AT90](#)