


HONEYWELL
PART NUMBER

2TP201 SERIES CHART 1

REV	DOCUMENT	CHANGED BY	CHECK
7	0011613	VKR 04MAR05	AK

△ 6 △ 5	CATALOG LISTING	△CIRCUIT MADE WITH BUTTON DEPRESSED ON			ELECTRICAL DATA
		LUG SIDE (1-2, 4-5)	CENTER (1-2, 4-5)	OPPOSITE LUG (2-3, 5-6)	
FAA PMA	2TP201-1	ON	OFF	ON	L191 15A 125, 250, 277 VAC 1/2HP 125 VAC 1HP 250, 277 VAC 5A 125 VAC "L" UL CE
	2TP201-2	OFF	NONE	ON	
	2TP201-3	ON	NONE	ON	
	2TP201-21	NONE	OFF	ON	
	Ⓢ	NONE	ON	ON	
	2TP201-4	MOM OFF	NONE	ON	L192 10A 125, 250, 277 VAC 1/4HP 125 VAC, 1/2HP 250, 277 VAC 3A 125 VAC "L" UL CE
	2TP201-5	MOM ON	OFF	ON	
	2TP201-6	MOM ON	NONE	OFF	
FAA PMA	2TP201-7	MOM ON	OFF	MOM ON	
FAA PMA	Ⓒ	MOM ON	NONE	ON	
	Ⓢ	NONE	ON	MOM ON	
	2TP201-61	MOM ON	OFF	NONE	



NOTES


- 1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
- 2 - APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS
- 3 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
- 4 - SCREWS FURNISHED UNASSEMBLED
- 5 - FAA PMA MUST BE MARKED ON SWITCH
- 6 - FOR MANUFACTURING DETAILS SEE THE CORRESPONDING ASSEMBLY DRAWING FOR EACH LISTING FOR FAA-PMA

REPLACES: 2TP201 SERIES

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:

NO PLACE	X	±	
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	
ANGLES		±	

THIRD ANGLE PROJECTION



DRAWN	SM	09JUL94
CHECK	KAG	07JUL94
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		

RASTER

Honeywell

TITLE

SWITCH - TOGGLE
FLUSH KEY

SIZE	TYPE	DRAWING NAME	REV
A	I	2TP201 SERIES CHART 1	7
SCALE	FULL	WEIGHT: .14LB EST	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[2TP201-1](#) [2TP201-2](#) [2TP201-3](#) [2TP201-5](#) [2TP201-7](#)