

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-2RW80147-P4

APR9030

M BZ-2RW80147-P4

PAGE 1 OF 1

REPLACES

PR-1568

RELEASE NO.

21EFB06

RU

CHECK

0

A	CO- 73287-G
---	----------------

20 OCT 93 0

B	CO- 75367B
---	---------------

L J F

3 MAR 94	
C CO-80988	

SECRET

5 JUN 95		✓ 2
D	CO-	

D	77863	U
	2 LW	

G J W
7 MAY 96

E	C093346	U
---	---------	---

DLT 16 SEP 98	70
------------------	----

F 0018656

NM
21 FEB 06

1	2
---	---

[illegible]

		9
--	--	---

			BA
--	--	--	----

	СХ
--	----

		CHE
--	--	-----

	70
--	----

20


TEI

RM	1A	DRAWN	17
----	----	-------	----

378 -	D	H
-------	---	---

F
D-503
S R

0	1
---	---



NOTE

NOTE
① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX
DIAMETER ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE----- 6 OZ MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE----- 1 1/2 OZ MIN	UNDERWRITERS' LAB. INC. LISTED RATING -L96- 15A-125, 250, OR 480 VAC 1/2 A-125 VDC; 1/4 A-250 VDC 1/8 HP-125 VAC; 1/4 HP-250 VAC	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL-----.003-.020	-L288- -L306- -L315-	TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
OVERTRAVEL-----.094 MIN	CE  05   16A 250V  T85 5E4	WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2RW80147-P4](#)