

**MICRO SWITCH**  
a Honeywell Division

FED.MFG.CODE 91929

## SWITCH - BASIC

CATALOG LISTING

BZ-2RW8055516T

AQB0037

BZ-2RW8055516T

M

DRAWING  
NUMBER

4

ISSUE

REPLACES X94427-BZ

RELEASE NO. PR-19660

CHECK

### REVISIONS

A	CO-77589
	TSM
	30 MAR 94
B	CO93346
	D L T
	17 SEP 98
C	0017580
	TSG
	09 JAN 06

CHECK

09 JAN 06

RJ

CHECK

3 JAN 92

GR T

3 JAN 92

3 JAN 92


3 JAN 92

3 JAN 92

3 JAN 92

3 JAN 92

3 JAN 92




### NOTES:

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



### CHARACTERISTICS

OPERATING FORCE ----- 6 OZ MAX  
RELEASE FORCE ----- 1 1/2 OZ MIN  
DIFFERENTIAL TRAVEL ----- .003-.020  
OVERTRAVEL ----- .094 MIN

### ELECTRICAL DATA

CONTACT ARRANGEMENT  
S P D T

L96

15A 125, 250 OR 480 VAC  
1/8HP 125 VAC, 1/4HP 250 VAC  
1/2A 125 VDC, 1/4A 250 VDC

L288  
L306  
L315

16A 250V ~ T85 5E4



SCALE FULL DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ±.030

TWO PLACE (.00) ±.015

THREE PLACE (.000) ±.005

ANGLES ±

WEIGHT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2RW8055516T](#)