





HONEYWELL PART NUMBER
-

REV	DOCUMENT	CHANGED BY	CHECK
4	0041136	SS 25JUN08	BLR



NOTE  
1 - METRIC MOUNTING HOLES

RELEASE NO. PR-19189	CATALOG LISTING CW-B1740
REPLACES -	

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:		DRAWN	TSM	14JUN99	Honeywell								
OPERATING FORCE --- 150 GRAMS MAX		CONTACT ARRANGEMENT S P D T				CHECK	JAF	14JUN99							TITLE  SWITCH, BASIC		
RELEASE FORCE ----- 25 GRAMS MIN		L215  15.1A 1/2HP 125, <u>250</u> OR 277 VAC 1/2A 125 VDC 1/4A 250 VDC; 5A 125 VAC "L"  		NO PLACES X ± -		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE B	TYPE I	CAGE CODE -			
DIFFERENTIAL TRAVEL ---- .002-.010				ONE PLACE .X ± 0.030													
OVERTRAVEL ----- .050 MIN				TWO PLACE .XX ± 0.015													
FREE POSITION ----- .625 MAX				THREE PLACE .XXX ± 0.005													
RELEASE TRAVEL ----- .010 MIN						ANGLES X ± -		Pro/ENGINEER 2D			SCALE -		SHEET 1 OF 1				
																	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-1C18D8](#)