

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-2RW876-PC2**BZ-2RW876-PC2**

PAGE 1 OF 1

MDRAWING
NUMBERISSUE
4

REPLACES

RELEASE NO. PR-17383

CHECK

REVISIONS

A	CO-67851-A
	BAB
	15 AUG 90
B	CO-77592
	DAW
	15 AUG 94
C	CO93346
	DLT
	2 SEP 98

CHECK

89

JUN

JAP

JUN

JUN

JUN

JUN


JUN

JUN

FORMTEK

FO-30376

DRAWN



NOTE

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $.139$ MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ——— 6 OZ MAX

RELEASE FORCE ——— 1 1/2 OZ MIN

DIFFERENTIAL TRAVEL ——— .004 — .025

OVERTRAVEL ——— .141 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

S P D T

L74 15A 125, 250, OR 480 VAC 2A 600 VAC
 1/8 HP 125 VAC, 1/4 HP 250 VAC
 1/2A 125 VDC, 1/4A 250 VDC

L288
L299
L306

16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) $\pm .030$
 TWO PLACE (.00) $\pm .015$
 THREE PLACE (.000) $\pm .005$
 ANGLES $\pm$

WEIGHT .073 LB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2RW876-PC2](#)