





CATALOG LISTING
DT-2RV-A7



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

| CHARACTERISTICS | ELECTRICAL DATA | SCALE FULL |
|---------------------------------|---|---------------------------|
| OPERATING FORCE-----3 1/2-6 OZ | CONTACT ARRANGEMENT D P D T | DO NOT SCALE PRINT |
| RELEASE FORCE-----1 OZ MIN | UL LISTED-FILE E12252 | UNLESS OTHERWISE NOTED |
| PRETRAVEL-----1.110 MAX | CODE L59 | DIMENSIONS ARE IN INCHES |
| DIFFERENTIAL TRAVEL-----490-755 | 10A-125 OR 250 VAC | TOLERANCES ARE: |
| OVERTRAVEL-----062 MIN | 0.3A-125 VDC; 0.15A-250 VDC | ONE PLACE (.0) ±.030 |
| |  | TWO PLACE (.00) ±.015 |
| | | THREE-PLACE (.000) ±.005 |
| | | ANGLES ± |
| | | WEIGHT 080 LB |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[DT-2RV-A7](#)