

FED. MFR. CODE 91929

MT-4RV2-A28

CHARACTERISTICS		ELECTRICAL DATA				SCALE FULL	
OPERATING FORCE-----2 3/4 OZ. MAX. (A)		CONTACT ARRANGEMENT S. P. D. T.				DO NOT SCALE PRINT	
RELEASE FORCE-----1/4 OZ. MIN. (A)		NON-POLARIZED	VOLTS D-C 125 250	MOTOR 1/4 HP + —	RESISTIVE 10 AMPS 1.5 TO 3.0*	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	
DIFFERENTIAL TRAVEL-----.065 MAX. (A)		POLARIZED OR NON- MAGNETICALLY MOUNTED	VOLTS D-C 125 250	MOTOR 1/2 HP + —	RESISTIVE 10 AMPS 1.5 TO 3.0*	TOLERANCES ARE:	
OVERTRAVEL-----.031 MIN.		* NOT SUITABLE FOR USE AT LESS THAN 1.5 AMPS + WILL NOT BREAK LOCKED ROTOR CURRENT				ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±	
		UND. LAB. INC. LISTED RATING (NON-POLARIZED) (C) - L155- 10 A-125 VDC OR AC; 1/4 HP-125 VDC OR AC				WEIGHT	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[MT-4RV2-A28](#)