

APY0293

MICRO SWITCH
a Honeywell Division

FED.MFG.CODE 91929

SWITCH-BASIC

X101334-BZ

REPLACES

PR-22777

RELEASE NO	
------------	--

CHECK

CHECK	
-------	--

29 AUG 05

RJ

DATE TIME LOCATION REMARKS 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30 31 32 33 34 35 36 37 38 39 40 41 42 43 44 45 46 47 48 49 50 51 52 53 54 55 56 57 58 59 60 61 62 63 64 65 66 67 68 69 70 71 72 73 74 75 76 77 78 79 80 81 82 83 84 85 86 87 88 89 90 91 92 93 94 95 96 97 98 99 100	DATE TIME LOCATION REMARKS 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30 31 32 33 34 35 36 37 38 39 40 41 42 43 44 45 46 47 48 49 50 51 52 53 54 55 56 57 58 59 60 61 62 63 64 65 66 67 68 69 70 71 72 73 74 75 76 77 78 79 80 81 82 83 84 85 86 87 88 89 90 91 92 93 94 95 96 97 98 99 100
--	--


T S M	4 JUNE 97
-------	-----------

BZ-2RW84467-A2

3

FORMTEK

DRAWN




NOTE

1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $\varnothing .139$ MAX ON $1.000 \pm .002$ CENTERS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE - - - - 3/4 OZ MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
DIFFERENTIAL FORCE - - - 1/2 OZ MAX	L96	ONE PLACE	(.0)	±.030
PRETRAVEL - - - - - .562 MAX	15A 125, <u>250</u> OR 480 VAC	TWO PLACE	(.00)	±.015
DIFFERENTIAL TRAVEL - - .023-.080	1/8HP 125 VAC, 1/4HP <u>250</u> VAC	THREE PLACE	(.000)	±.005
OVERTRAVEL - - - - - .266 MIN	1/2A 125 VDC, 1/4A 250 VDC	ANGLES		±
	-L288- -L306- -L315-	WEIGHT		
	   			
	16A 250V  T85 5E4			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2RW84467-A2](#)