

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL INC.
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING
BZ-7RW82132T-S


AQL5320

M BZ-7RW82132T-S
PAGE 1 OF 1

RELEASE NO. PR-16526 REPLACES X85313-BZ

DRAWING NUMBER
7
ISSUE


REVISIONS	
A	CO67209 J A P 5 MAY 90
B	CO- 69351-D JWB 18 JUL 91
C	CO- 75204-B WJC 1 FEB 94
D	CO- 77588 K D R 29 MAR 94
E	CO93346 DLT 23 SEP 98
F	0015138 SPK 29 AUG 05



6-32 UNC X .219 REF BINDING HEAD TERMINAL SCREW AND LOCKWASHER (SEMS)(3)

NOTE
1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
		OPERATING FORCE ----- 5 OZ MAX RELEASE FORCE ----- 3/4 OZ MIN DIFFERENTIAL TRAVEL ----- .040-.090 OVERTRAVEL ----- .156 MIN	
CONTACT ARRANGEMENT S P D T L197 15A 125, 250, 277 VAC 1/8 HP 125 VAC; 1/4 HP 250 VAC 1/2A 125 VDC; 1/4A 250 VDC -L288- -L306- -L315-		CE EN 05 EC 16A 250V ~ T85 5E4	

FORMTEK
FO-52848-B
DRAWN
KAG 27 JUN 88 CHECK JAP 28 JUN 88

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-7RW82132T-S](#)