

<b>MICRO SWITCH</b> a Honeywell Division <small>FED. MFG. CODE 91929</small>		SWITCH-BASIC		<small>CATALOG LISTING</small> <b>V7-7A19D8</b>	
				<b>CW-C6076</b>	

CATALOG LISTING

**V7-7A19D8**

PAGE 1 OF 1

REPLACES X99905-V7

RELEASE NO. PR-21744

CHECK

30JAN12

CHECK

30JAN12

CMH

30JAN12

CHECK

30JAN12

DCS

21 JUN 95

ISSUE

**M**

2

REVISIONS

A	0085964	SBH	30JAN12

DRAWN

RASTER

PLASTIC PLUNGER

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS	ELECTRICAL DATA	SCALE
OPERATING FORCE — — — — 8 OZ MAX RELEASE FORCE — — — — 2 OZ MIN DIFFERENTIAL TRAVEL — .002 — .015 OVERTRAVEL — — — — .050 MIN FREE POSITION — — — — .625 MAX RELEASE TRAVEL — — — — .010 MIN	CONTACT ARRANGEMENT S P D T  L162 5A 125; <u>250</u> 277 VAC 1/10 HP <u>250</u> VAC  <div style="display: flex; justify-content: center; gap: 20px;"> </div>	<div style="display: flex; justify-content: space-between;"> <span>NONE</span> <span>DO NOT SCALE PRINT</span> </div> <p><b>UNLESS OTHERWISE SPECIFIED TOLERANCES ARE</b></p> ONE PLACE ( .0 ) ±.030 TWO PLACE ( .00 ) ±.015 THREE PLACE ( .000 ) ±.005 ANGLES ± WEIGHT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-7A19D8](#)