

V7-7A19D8-374

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Basic Switches](#) : [Premium V-Basic Switches](#) : [V7](#))



V7 Series Miniature Basic Switch, Single Pole Normally Open Circuitry, 11 A at 250 Vac, Curved Tip Actuator, 1,98 N [7.0 oz] Maximum Operating Force, Silver Contacts, Quick Connect Termination

Actual product appearance may vary.

Product Specifications

Switch Type	MICRO SWITCH™ Miniature 15,9 mm H x 10,2 mm W x 28,8 mm L [0.63 in H x 0.4 in W x 1.14 in L]
Sealed	No
Ampere Rating	11 A
Circuitry	SPNO
Actuator	Curved Tip Lever
Termination	Quick Connect
Operating Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Voltage	250 Vac
Actuator Length	25,9 mm [1.02 in]
Contact Type	Silver
Operating Force (OF)	1,98 N [7.0 oz] max.
Release Force	0,28 N [1.0 oz] min.
Pretravel (PT)	2,03 mm [0.080 in] max.
Overtravel (OT)	1,19 mm [0.047 in] min.
Differential Travel (DT)	0,46 mm [0.018 in] max.
Operating Position (OP)	21,5 mm ±0,94 mm [0.847 ±0.037 in]
Housing Material	PCT Polyester Thermoplastic
Agency Approvals and Standards	UL, CSA, ENEC
Mounting Centers	22,2 mm [0.88 in]
Tightening Torque	0,56 N m [5.0 in lb]
Weight	8 g [0.3 oz]
Package Height	15,9 mm [0.63 in]
Package Width	10,3 mm [0.40 in]
Package Length	27,8 mm [1.09 in]
Comment	ENEC coverage available dependign upon electrical rating mated w ith; CE: 61058-1; UL: E12252; CSA: LR41370
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap switches
Series Name	V7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-7A19D8-374](#)