

V7-6A17D8-057

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Basic Switches](#) : [Premium V-Basic Switches](#) : [V7](#))



Actual product appearance may vary.

V7 Series Miniature Basic Switch, Single Pole Double Throw Circuitry, 5 A at 250 Vac, Straight Steel Actuator, 100 gf Maximum Operating Force, Silver Contacts, Quick Connect Termination, CSA|UL

[click here to download Hi-Res image](#)

Product Specifications

Switch Type	MICRO SWITCH™ Miniature 15,9 mm H x 10,2 mm W x 28,8 mm L [0.63 in H x 0.4 in W x 1.14 in L]
Sealed	No
Ampere Rating	5 A
Circuitry	SPDT
Actuator	Straight Lever
Termination	Quick Connect
Operating Temperature	-40 °C to 82 °C [-40 °F to 180 °F]
Voltage	250 Vac
Actuator Length	62,2 mm [2.45 in]
Contact Type	Silver
Operating Force (OF)	100 gf max.
Release Force	15 gf min.
Pretravel (PT)	8,0 mm [0.315 in] max.
Overtravel (OT)	3,68 mm [0.145 in] min.
Differential Travel (DT)	1,7 mm [0.067 in] max.
Operating Position (OP)	15,3 mm ±0,558 mm [0.603 ±0.022 in]
Housing Material	PCT Polyester Thermoplastic
Agency Approvals and Standards	UL, CSA
Mounting Centers	22,2 mm [0.88 in]
Tightening Torque	0,56 N m [5.0 in lb]
Weight	8 g [0.3 oz]
Package Height	15,9 mm [0.63 in]
Package Width	10,3 mm [0.40 in]
Package Length	27,8 mm [1.09 in]
Comment	CE: 61058-1; UL: E12252; CSA: LR41370
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap switches
Series Name	V7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-6A17D8-057](#)