

SZR-LY2-N1-DC24V

([Home](#) : [Products](#) : [basics](#) : [Switches](#) : [Relays](#) : [SZR-LY](#))



SZR-LY General Purpose Relay: LED Indicator; Plug-in/Solder Terminal; DPDT; 24 Vdc

Actual product appearance may vary.

Product Specifications

Current Rating	10 A
Contact(s)	DPDT
Terminal	Solder/Plug-In
Options	LED Indicator
Resistive Load	24 V, 10 A
Inductive Load	24 V, 5 A
Switching (Resistive Load)	240 W
Switching (Inductive Load)	120 W
Contact Rating	125 Vdc
Coil Input Voltage	24 Vdc
Rated Current at 50 Hz	36.9 mA
Rated Current at 60 Hz	36.9 mA
Coil Resistance	650 ohms
Power Consumption	0.9 W
Dropout Voltage (% of Rated Voltage)	10 % min.
Pick-Up Voltage (Must Operate)	80 % max. of the Rated Coil Voltage
Voltage	110 % of the rated coil voltage
Operating Voltage	80 % of the rated coil voltage
Operate Time	25 ms max.
Release Time	25 ms. max
Ambient Temperature	-25 °C to 70 °C [-13 °F to 158 °F]
Ambient Humidity	45 % RH to 85 % RH
Contact Material	Silver Cadmium Oxide
Contact Resistance	50 mOhm max.
Operating Frequency (Mechanical)	18,000 Operations/Hour
Operating Frequency (Electrical)	1800 Operations/Hour
Vibration Resistance	10 Hz to 55 Hz at Double Amplitude of 1.0 mm
Shock Resistance	1000 m/s2 (Approx. 100 G)
Weight	35 g [1.24 oz]
Agency Approvals and Standards	UL, CE

Product Specifications

UL File #	E#150950
Expected Mechanical Life	dc - 100 Million Operations min.
Comment	LED Indicator; Solder/Plug-in; DPDT
Availability	Global
Series Name	SZR-LY

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[SZR-LY2-N1-DC24V](#)