

SZL-VL-G

([Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Limit Sw itches](#) : [MICRO SWITCH™ Global Limit Sw itches](#) : [SZL-VL](#))



Actual product
appearance may vary.

**General Purpose Lim it Switch, VL Series; Wobble/Coil Spring ; 1NC 1NO SPDT;
Double Break**



SZL-VL-G
highres photo



SZL-VL-G
low res photo

Product Specifications

Availability	North-America; Asia-Pacific
Operating Force (OF)	0,88 N [0.2 lb] max.
Pretravel (PT)	30 mm [1.18 in] max.
Overtravel (OT)	20 mm [0.788 in]
Product Type	Miniature Limit Sw itches
Actuator	Wobble - Coil Spring
Lever Type	None
Circuitry	1NC 1NO SPDT Double Break
Ampere Rating	5.0 A/0.4 A
Supply Voltage	250 Vac/125 Vdc max.
Housing Material	Zinc Die-Cast/Plastic
Termination Type	Cable Gland
Series Name	SZL-VL
Shock	10 g max.
Vibration	55 Hz at double amplitude of 1,5 mm
Sealing	IP64
UL File #	E150950
Expected Mechanical Life	up to 10 Million
Operating Temperature	-20 °C to 60 °C [-4 °F to 140 °F]
Agency Approvals and Standards	UL, cULus, CE
Sealed	Industrial

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[SZL-VL-G](#)