

SL1-AK

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Limit Switches](#) : [MICRO SWITCH™ Medium-Duty Limit Switches](#) : [SL1](#))



Series SL1: Top Roller Plunger; 1 NC 1 NO SPDT Snap Action; Compression Fitting

Actual product appearance may vary.

Product Specifications

Availability	North America; Asia-Pacific; Latin America
Operating Force (OF)	11,8 N [2.65 lb] max.
Release Force	4,90 N [1.10 lb] min.
Pretravel (PT)	1,5 mm [0.06 in] max.
Overtravel (OT)	3,0 mm [0.118 in] max.
Differential Travel (DT)	0,1 mm [0.004 in] max.
Product Type	MICRO SWITCH™ Miniature Limit Switches
Actuator	Top Roller Plunger
Lever Type	None
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	0.1 A
Supply Voltage	125 Vac/30 Vdc
Housing Material	Zinc Die-Cast
Termination Type	Cable Gland
Series Name	SL1
Sealing	IP67; NEMA 3, 4, 13
Operating Temperature	-10 °C to 70 °C [14 °F to 160 °F]
Comment	M3 Terminal screws; 5,8 mm to 9,6 mm outside cable diameter; Gold contacts
Sealed	Industrial
Contact Material	Gold

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[SL1-AK](#)