

OP-AR20

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Limit Switches](#) : [MICRO SWITCH™ Global Limit Switches](#) : [OP](#))



Enclosed Switch Series OP: Side Rotary, No lever furnished, 1NO 1NC Snap Action SPDT, CW actuation

Actual product appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	0,08 N to 0,23 N [12 in lb to 2 in lb] max.
Release Force	6.25 oz-in min.
Pretravel (PT)	8°
Overtravel (OT)	90°
Differential Travel (DT)	25°
Product Type	Enclosed Switches
Actuator	Side Rotary
Lever Type	-- No Lever --
Circuitry	1NC 1NO Snap Action, SPDT
Ampere Rating	15 A
Supply Voltage	125 Vac, 250 Vac, 480 Vac
Housing Material	Aluminum Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Series Name	OP
Sealing	NEMA 1, 3, 4, 13
UL File #	E12252
Comment	CW actuation. No lever furnished.
Agency Approvals and Standards	UL, CSA
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Switches

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[OP-AR20](#)