

MT-4RV-A28

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Basic Switches](#) : [Premium Large Basic Switches](#) : [MT](#))



Actual product
appearance may vary.

MT Series Standard Basic Switch, Single Pole Double Throw Circuitry, 10 A at 125 Vdc/Vac (non-polarized), Straight Lever Actuator, 0,56 N [2.0 oz] Max. Operating Force, Silver Contacts, Screw Termination, CSA, UL



[MT-4RV-A28
highres photo](#)



[MT-4RV-A28
low res photo](#)

Product Specifications

Switch Type	MICRO SWITCH™ Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]
Sealed	No
Ampere Rating	10 A
Circuitry	SPDT
Actuator	Straight Lever
Termination	Screw
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	125 Vac/125 Vdc
Actuator Length	63,5 mm [2.5 in]
Contact Type	Silver
Operating Force (OF)	0,56 N [2.0 oz] max.
Release Force	0,14 N [0.494 oz] min.
Pretravel (PT)	12,7 mm [0.50 in] max.
Overtravel (OT)	1,19 mm [0.047 in] min.
Differential Travel (DT)	2,16 mm [0.085 in] max.
Operating Position (OP)	19,1 mm ±0,76 mm [0.75 in ± 0.03 in]
Housing Material	Arc Resistant Melamine
Agency Approvals and Standards	UL, CSA
Mounting Centers	25,4 mm [1 in]
Tightening Torque	0,33 N m [3.0 in lb]
Weight	34,5 g [0.076 lb]
Package Height	24,1 mm [0.95 in]
Package Width	17,5 mm [0.69 in]
Package Length	49,3 mm [1.94 in]
Availability	Global
UNSPSC Code	39122209

Product Specifications

UNSPSC Commodity	39122209 Snap sw itches
Series Name	MT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[MT-4RV-A28](#)