

GSAC01B

([Home](#) : [Products](#) : [Machine Safety](#) : [MICRO SWITCH™](#) [Safety Sw itches](#) : [Electromechanical](#) : [GSS](#))



GSS Series , Safety Lim it Switch, 1NC/1NO Direct Opening, Snap Action, Top Pin Plunger, 20 mm , EN50041, Zinc Die-cast, Silver Contacts

Actual product appearance may vary.

Product Specifications

Product Type	Safety Limit Sw itch
Actuator	Top Pin Plunger
Sw itch Type	1NC/1NO Direct Opening, Snap Action
Contact Material	Silver
Termination Type	20 mm
Ampere Rating	100 mA to 10 A (Thermal)
Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Housing Type	EN50041
Series Name	GSS
Shock	50 g per IEC 68-2-27
Vibration	10 g per IEC 68-2-6
Sealing	IP67; NEMA 1, 4, 12, 13, EN60529
CSA File #	LR94369-3
UL File #	E37138, E157416
Agency Approvals and Standards	UL, CE, CSA, SIL 3 capable
Expected Mechanical Life	15 Million
Operating Temperature	-25 °C to 85 °C [-13 °F to 185 °F]
Availability	Global
UNSPSC Code	39122205
UNSPSC Commodity	39122205 Safety Sw itches
Comment	IEC 947-5-1, EN60947-5-1, UL508

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[GSAC01B](#)