

BZE7-2RQ8-PG

([Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Limit Sw itches](#) : [MICRO SWITCH™ Medium-Duty Limit Sw itches](#) : [E7/V7](#))



Actual product
appearance may vary.

Enclosed Switches Series E7: Top Roller Plunger Actuator; 1NC 1NO SPDT
Snap Action; PG13,5 conduit



BZE7-2RQ8-PG
highres photo



BZE7-2RQ8-PG
low res photo

Product Specifications

Availability	Global
Operating Force (OF)	2,50 N to 3,61 N [9 oz to 13 oz]
Release Force	1,11 N [0.25 lb] min.
Pretravel (PT)	0,38 mm [0.015 in] max.
Overtravel (OT)	3,55 mm [0.140 in] min.
Differential Travel (DT)	0,05 mm [0.002 in] max.
Product Type	Enclosed Sw itches
Actuator	Top Roller Plunger
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	15 A Ind./0.5 A Res./0.25 A Res.
Supply Voltage	125 Vac, 250 Vac, 480 Vac/125 Vdc/250 Vdc
Housing Material	Aluminum Die-Cast
Termination Type	PG13,5
Housing Type	Split Housing, Side Mount
Series Name	E7/V7
Sealing	IP50
Operating Temperature	-30 °C to 71 °C [-22 °F to 160 °F]
Comment	Without seal boot on plunger, Roller parallel to long axis of sw itch
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Sw itches
Sealed	Industrial

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZE7-2RQ8-PG](#)