

BZE7-2RN2-PG

([Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Limit Sw itches](#) : [MICRO SWITCH™ Medium-Duty Limit Sw itches](#) : [E7/V7](#))



Enclosed Switches Series E7: Top Roller Arm Actuator, Adjustable with Steel Roller; 1NC 1NO SPDT Snap Action; PG13,5 conduit

Actual product appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	2,78 N to 5,56 N [10 oz to 20 oz]
Release Force	1,67 N [6 oz] min.
Pretravel (PT)	4,78 mm [0.188 in] max.
Overtravel (OT)	5,56 mm [0.219 in] min.
Differential Travel (DT)	0,15 mm [0.006 in] max.
Product Type	Enclosed Sw itches
Actuator	Top Roller Arm
Lever Type	Roller - Adjustable
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	15 A Ind./0.5 A Res./0.25 A Res.
Supply Voltage	125 Vac, 250 Vac, 480 Vac/125 Vdc/250 Vdc
Housing Material	Aluminum Die-Cast
Termination Type	PG13,5
Housing Type	Split Housing, Side Mount
Series Name	E7/V7
Sealing	IP65
Operating Temperature	-30 °C to 71 °C [-22 °F to 160 °F]
Comment	With seal boot on plunger; Lever field adjustable 360° horizontally and 225° vertically
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Sw itches
Sealed	Industrial

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZE7-2RN2-PG](#)