

BZE6-2RN193

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Limit Switches](#) : [MICRO SWITCH™ Medium-Duty Limit Switches](#) : [E6/V6](#))



Enclosed Switches Series E6: Top Plunger Actuator; 1NC 1NO SPDT Snap Action; 1/2 in - 14NPSM conduit

[click here to download Hi-Res image](#)

Actual product
appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	2,50 N to 6,67 N [9 oz to 24 oz]
Release Force	1,11 N [0.25 lb] min.
Overtravel (OT)	5,56 mm [0.219 in] min.
Differential Travel (DT)	0,05 mm [0.002 in] max.
Product Type	Enclosed Switches
Actuator	Top Plunger
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	15 A Ind./2 A Ind./0.5 A Res./0.25 A Res.
Supply Voltage	125 Vac, 250 Vac, 480 Vac/600 Vac/125 Vdc/250 Vdc
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14NPSM Conduit
Housing Type	Split Housing, Side Mount
Series Name	E6/V6
Sealing	IP66; NEMA 1, 3, 4
UL File #	E12252
Operating Temperature	-40 °C to 70 °C [-40 °F to 158 °F]
Comment	With seal boot on plunger
Agency Approvals and Standards	UL, CSA
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Switches
Sealed	Industrial

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZE6-2RN193](#)