

## BX4A3K-1A

( [Home](#) : [Products](#) : [basics](#) : [Sw itches](#) : [MICRO SWITCH™](#) [Hazardous Location Sw itches](#) : [BX Sw itches](#) )



**Lever Included**

Series BX Non Plug-in: Side Rotary; 1NC 1NO SPDT Snap Action; 20 mm

[click here to download Hi-Res image](#)

Actual product  
appearance may vary.

### Product Specifications

Availability	Global
Pretravel (PT)	15°
Overtravel (OT)	60° min.
Differential Travel (DT)	5° max.
Product Type	MICRO SWITCH™ Weather-Sealed, Explosion-Proof Limit Sw itches/European and Global Approvals
Actuator	Side Rotary
Lever Type	1.5 in Fixed Length Lever w ith front mounted Nylon Roller (.75 in dia. x .25 in w ide)
Circuitry	1NC 1NO SPDT Snap Action, Double-Break
Ampere Rating	10 A (Thermal)
Supply Voltage	600 Vac and 250 Vdc max.
Housing Material	Aluminum
Termination Type	20 mm Conduit
Housing Type	BX Non Plug-in
Series Name	BX Sw itches
Sealing	IP67; NEMA 1, 3, 4, 6, 13
ATEX File #	Sira 00ATEX1037X
IEC Ex	Yes
Operating Temperature	-40 °C to 70 °C (-40 °F to 158 °F)
Comment	Lever Included; EExd IIC T6 category II 2 GD, SIRA 00ATEX 1037X
Agency Approvals and Standards	ATEX, IEC Ex, NEPSI
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Sw itch
Sealed	Explosion-proof
Is Listing Lead (Pb) Free	Yes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BX4A3K-1A](#)