

AML32FBK4AC

([Home](#) : [Products](#) : [basics](#) : [Sw itches](#) : [MICRO SWITCH™ Pushbuttons and Manual Sw itches](#) : [AML32](#))

Image Not Available

AML32 Series, Solid State Pushbutton, Rectangular, Standard Bezel, Lighted, 1 Neon Lamp, DPST NO Form X, Momentary Action, Snap in panel mount

Actual product appearance may vary.

Product Specifications

Product Type	MICRO SWITCH™ Pushbutton
Housing Type	Rectangular
Circuitry	DPST NO Form X
Action	Momentary Action
Mounting	Snap-in Panel
Lamp Type	Lighted, 1 Neon Lamp
Termination	.187 x .020 (Solder or Quick-Connect)
Ampere/Voltage Range (Resistive Load)	0.4-10 A @ 0.5-250 Vac 0.4-10 A @ 0.5-30 Vdc
LED/Lamp/Neon Voltage	125 Vac
LED/Neon Color	Yellow
Comment	use AML52-N button
Availability	Global
UNSPSC Code	30211913
UNSPSC Commodity	30211913 Push button sw itches
Series Name	AML32

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[AML32FBK4AC](#)