

142-302LAG-RB2

([Home](#) : [Products](#) : [Sensors](#) : [Temperature Sensors](#) : [Discrete Thermistors](#) : [143](#))



143 Series, 2,54 mm [0.1 in] disc thermistor with leads and epoxy, 3,000 Ohm resistance, $\pm 10.0\%$ tolerance, 25/85 BETA = 3974

Actual product appearance may vary.

Product Specifications

Availability	Global
Resistance	3,000 Ohm
Tolerance	$\pm 10.0\%$
Accuracy	25 °C [77 °F]
Beta	3974
Operating Temperature	-60 °C to 125 °C [-76 °F to 257 °F]
Diameter	3,81 mm [0.15 in]
Termination Material	Tinned copper
Lead Length	38,1 mm [1.50 in]
Time Constant in Air	10.0 s
Dissipation Constant	3,0 m/W°C
Series Name	143
R-T Curve	16

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[142-302LAG-RB2](#)