

135-253LAG-J01

( [Home](#) : [Products](#) : [Sensors](#) : [Temperature Sensors](#) : [Discrete Thermistors](#) : [135](#) )



135 Series, glass encapsulated chip DO-35 type, 25,000 Ohm resistance,  $\pm 10.0\%$  tolerance, 25/85 BETA = 3974

Actual product appearance may vary.

Product Specifications

Availability	Global
Resistance	25,000 Ohm
Tolerance	$\pm 10.0\%$
Accuracy	25 °C [77 °F]
Beta	3974
Operating Temperature	-60 °C to 300 °C [-76 °F to 572 °F]
Diameter	2,0 mm [0.080 in]
Termination Material	Tinned copper-clad steel
Lead Length	28,6 mm [1.125 in]
Time Constant in Air	4.0 s
Dissipation Constant	2,5 m/W°C
Series Name	135
R-T Curve	<b>16</b>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[135-253LAG-J01](#)