

129-402VND-Q01

([Home](#) : [Products](#) : [Sensors](#) : [Temperature Sensors](#) : [Discrete Thermistors](#) : [129](#))



129 Series, matched large glass probe, 4,000 Ohm resistance, $\pm 2.0\%$ tolerance, 25/85 BETA = 3518

Actual product appearance may vary.

Product Specifications

Availability	Global
Resistance	4,000 Ohm
Tolerance	$\pm 2.0\%$
Accuracy	15 °C to 25 °C [59 °F to 77 °F]
Beta	3518
Operating Temperature	-60 °C to 300 °C [-76 °F to 572 °F]
Diameter	5,08 mm [0.20 in]
Termination Material	Dumet lead
Lead Length	50,8 mm [2.00 in]
Time Constant in Air	22.0 s
Dissipation Constant	1,0 m/W°C
Series Name	129
R-T Curve	11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[129-402VND-Q01](#)