

112TW1-70E

([Home](#) : [Products](#) : [basics](#) : [Sw itches](#) : [MICRO SWITCH™](#) [Toggle Sw itches](#) : [TW](#))



TW Series Toggle Switch, 2 pole, 3 position, IWTS terminal, Locking Lever

Actual product appearance may vary.

Product Specifications

| | | | |
|---------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| Product Type | MICRO SWITCH™ Toggle Sw itch | | |
| Ampere/Voltage Range (Resistive Load) | 0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc 0.1 A to 5.0 A at 0.5 Vac to 115 Vac | | |
| Circuitry | DPDT | | |
| Action | 3 position | | |
| Circuitry/Operating action | <div><div><div>Keyway Momentary Position</div><div>3 2 1 6 5 4 ON</div></div><div><div>Center Maintained Position</div><div>3 2 1 6 5 4 ON</div></div><div><div>Opposite Keyway Momentary Position</div><div>3 2 1 6 5 4 ON</div></div></div> | | |
| Mounting | Bushing 15/32 in | | |
| Termination | IWTS | | |
| Lever Type | Locking | | |
| Lever Lock | <div>Locked in center position</div> | | |
| Comment | Fine silver contacts | | |
| Availability | Global | | |
| UNSPSC Code | 39122211 | | |
| UNSPSC Commodity | 39122211 Toggle Sw itch | | |

Product Specifications

Series Name

TW

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[112TW1-70E](#)