

914CE3-12K

( [Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Limit Sw itches](#) : [MICRO SWITCH™ Medium-Duty Limit Sw itches](#) : [914CE](#) )



Miniature Enclosed Switches Series 914CE: Cross Roller Plunger (90° Rotated Plunger); 1NC 1NO SPDT Snap Action; 12 foot Cable

Actual product appearance may vary.

Product Specifications

|                                |                                                  |
|--------------------------------|--------------------------------------------------|
| Availability                   | Global                                           |
| Operating Force (OF)           | 11,8 N [2.65 lb] max.                            |
| Release Force                  | 4,4 N [0.99 lb] max.                             |
| Pretravel (PT)                 | 1,0 mm ±0,5 mm [0.04 in ±0.02 in]                |
| Overtravel (OT)                | 3,0 mm [0.118 in] min.                           |
| Differential Travel (DT)       | 0,1 mm [0.004 in] max.                           |
| Product Type                   | MICRO SWITCH™ Miniature Limit Sw itches          |
| Actuator                       | Cross Roller Plunger (90° Rotated Plunger)       |
| Lever Type                     | None                                             |
| Circuitry                      | 1NC 1NO SPDT Snap Action                         |
| Ampere Rating                  | 5 A (Thermal)                                    |
| Supply Voltage                 | 240 Vac                                          |
| Housing Material               | Zinc Die-Cast                                    |
| Termination Type               | 12 foot Cable                                    |
| Series Name                    | 914CE                                            |
| Sealing                        | IP66, IP67, IP68; NEMA 1, 2, 3, 3R, 4, 6, 6P, 13 |
| UL File #                      | E41859                                           |
| Expected Mechanical Life       | up to 10 Million                                 |
| Operating Temperature          | 0 °C to 70 °C [35 °F to 160 °F]                  |
| Comment                        | Bottom Exit Cable                                |
| Agency Approvals and Standards | UL, CE, CSA. IEC947-5-1, EN60947-5-1             |
| UNSPSC Code                    | 39122213                                         |
| UNSPSC Commodity               | 39122213 Limit Sw itches                         |
| Sealed                         | Industrial                                       |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[914CE3-12K](#)