

632NT91-6

([Home](#) : [Products](#) : [basics](#) : [Sw itches](#) : [MICRO SWITCH™ Toggle Sw itches](#) : [NT](#))



NT Series Toggle Switch, Panel stand-off feature, 2 pole flat base, 2 position, Quick Connect terminal, Standard Lever

Actual product appearance may vary.

Product Specifications

Product Type	MICRO SWITCH™ Toggle Sw itch
Ampere/Voltage Range (Resistive Load)	0.5 A to 18 A at 0.5 Vdc to 28 Vdc 0.5 A to 10 A at 0.5 Vac to 277 Vac 0.5 A at 250 Vdc 0.75 A at 115 Vdc
Circuitry	DPST
Action	2 position
Circuitry/Operating action	<div><div>Keyway Momentary Position 1 2 5 4 ON</div><div>Opposite Keyway Position 1 2 5 4 OFF</div></div>
Mounting	Bushing 15/32 in
Termination	Quick Connect
Lever Type	Standard
UL/CSA	L192: 10 A-125, 250, 277 Vac; 1/4 Hp-125 Vac; 1/2 Hp-250, 277 Vac; 3 A-125 Vac "L"
Comment	Panel stand-off feature, Sw itches are capable of w ithstanding a temperature of 160 °F continuously at full rated load
Availability	Global
UNSPSC Code	39122211
UNSPSC Commodity	39122211 Toggle Sw itch
Series Name	NT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[632NT91-6](#)