

631NT91-7-NH

([Home](#) : [Products](#) : [basics](#) : [Sw itches](#) : [MICRO SWITCH™ Toggle Sw itches](#) : [NT](#))



NT Series Toggle Switch, Panel stand-off feature, 1 pole flat base, 3 position, Quick Connect terminal, Standard Lever, No hardware

Actual product appearance may vary.

Product Specifications

Product Type	MICRO SWITCH™ Toggle Sw itch
Ampere/Voltage Range (Resistive Load)	0.5 A to 15 A at 0.5 Vdc to 28 Vdc 0.75 A at 115 Vdc 0.5 A to 10 A at 0.5 Vac to 7 Vac 0.5 A at 250 Vdc
Circuitry	SPDT
Action	3 position
Circuitry/Operating action	<div><div>Keyway Momentary Position</div><div>Center Position</div><div>Opposite Keyway Momentary Position</div></div> <div><div> 1 2 3 ON</div><div> 1 2 3 OFF</div><div> 1 2 3 ON</div></div>
Mounting	Bushing 15/32 in
Termination	Quick Connect
Lever Type	Standard
UL/CSA	L192: 10 A-125, 250, 277 Vac; 1/4 Hp-125 Vac; 1/2 Hp-250, 277 Vac; 3 A-125 Vac "L"
Comment	Panel stand-off feature, sw itches are capable of w ithstanding a temperature of 160 °F continuously at full rated load, No hardw are
Availability	Global
UNSPSC Code	39122211
UNSPSC Commodity	39122211 Toggle Sw itch
Series Name	NT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[631NT91-7-NH](#)