

62NT1-8-NH

( [Home](#) : [Products](#) : [basics](#) : [Sw itches](#) : [MICRO SWITCH™ Toggle Sw itches](#) : [NT](#) )



NT Series Toggle Switch, Panel stand-off feature, 2 pole step base, 2 position, Screw terminal, Standard Lever

Actual product appearance may vary.

Product Specifications

Product Type	MICRO SWITCH™ Toggle Sw itch
Ampere/Voltage Range (Resistive Load)	0.5 A to 10 A at 0.5 Vac to 277 Vac 0.75 A at 115 Vdc 0.5 A at 250 Vdc 0.5 A to 18 A at 0.5 Vdc to 28 Vdc
Circuitry	DPDT
Action	2 position
Circuitry/Operating action	<div><div><div>Keyway Momentary Position</div><div></div></div><div><div>Opposite Keyway Position</div><div></div></div></div>
Mounting	Bushing 15/32 in
Termination	Screw
Lever Type	Standard
UL/CSA	L192: 10 A-125, 250, 277 Vac; 1/4 Hp-125 Vac; 1/2 Hp-250, 277 Vac; 3 A-125 Vac "L"
Comment	Panel stand-off feature; Thermoplastic case; No hardw are
Availability	Global
UNSPSC Code	39122211
UNSPSC Commodity	39122211 Toggle Sw itch
Series Name	NT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[62NT1-8-NH](#)