

15LS1-4PG

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Limit Switches](#) : [MICRO SWITCH™ Medium-Duty Limit Switches](#) : [LS](#))



Enclosed Switches Series LS: Top Roller Plunger; 2NC 2NO DPDT Snap Action, Double Break; PG13,5 conduit; Compact/Non-Plug-in

Actual product appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	31,14 N [7 lb] max.
Release Force	8,90 N [2.0 lb] min.
Overtravel (OT)	5,56 mm [0.219 in] min.
Differential Travel (DT)	1,14 mm [0.045 in] max.
Product Type	MICRO SWITCH™ Compact Limit Switches
Actuator	Top Roller Plunger
Circuitry	2NC 2NO DPDT Snap Action, Double-Break
Ampere Rating	10 A Ind.
Supply Voltage	120 Vac/240 Vac
Housing Material	Zinc Die-Cast
Termination Type	PG13,5
Housing Type	Compact / Non Plug-In
Series Name	LS
Sealing	NEMA 1, 3, 4, 6, 13
Operating Temperature	-29 °C to 71 °C [-20 °F to 160 °F]
Comment	Roller assembly may be re-positioned 90 degrees.
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Switches
Sealed	Industrial

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[15LS1-4PG](#)