

32NT391-1-C08

([Home](#) : [Products](#) : [basics](#) : [Sw itches](#) : MICRO SWITCH™ Toggle Sw itches : NT)



NT Series Toggle Switch, 2 pole, 3 position, Quick Connect terminal, Special Design Lever

Actual product appearance may vary.

Product Specifications

Product Type	MICRO SWITCH™ Toggle Sw itch
Ampere/Voltage Range (Resistive Load)	0.5 A at 250 Vdc 0.75 A at 115 Vdc 0.5 A to 10 A at 0.5 Vac to 7 Vac 0.5 A to 15 A at 0.5 Vdc to 28 Vdc
Circuitry	DPDT
Action	3 position
Circuitry/Operating action	<div><div>Keyway Position</div><div><div><div>123</div><div>654</div></div><div>ON</div></div></div> <div><div>Center Position</div><div><div><div>123</div><div>654</div></div><div>OFF</div></div></div> <div><div>Opposite Keyway Position</div><div><div><div>123</div><div>654</div></div><div>ON</div></div></div>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[32NT391-1-C08](#)