

31NT391-2-C08

( [Home](#) : [Products](#) : [basics](#) : [Sw itches](#) : [MICRO SWITCH™ Toggle Sw itches](#) : [NT](#) )



NT Series Toggle Switch, 1 pole, 2 position, Quick Connect terminal, Tab Lever

Actual product appearance may vary.

Product Specifications

Product Type	MICRO SWITCH™ Toggle Sw itch
Ampere/Voltage Range (Resistive Load)	0.5 A to 20 A at 0.5 Vdc to 28 Vdc 0.75 A at 115 Vdc 0.5 A at 250 Vdc 0.5 A to 15 A at 0.5 Vac to 277 Vac
Circuitry	SPST
Action	2 position
Circuitry/Operating action	<div><div>Keyway Position</div><div>2 3 OFF</div></div> <div><div>Opposite Keyway Position</div><div>2 3 ON</div></div>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[31NT391-2-C08](#)