

23AC82

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Basic Switches](#) : [Standard Miniature and Subminiature Switches](#) : [AC](#))



AC Series Door Switch, Single Pole Double Throw Circuitry, 5 A at 250 Vac, Rod Actuator, Silver Contacts, Quick Connect Termination

Actual product appearance may vary.

Product Specifications

Switch Type	Door 38,1 mm H x 12,7 mm W x 38,1 mm L [1.5 in H x 0.5 in W x 1.5 in L]
Sealed	No
Ampere Rating	5 A
Circuitry	SPDT
Actuator	Rod
Termination	Quick Connect
Operating Temperature	-18 °C to 82 °C [-65 °F to 180 °F]
Voltage	250 Vac
Contact Type	Silver
Operating Position (OP)	5,16 mm [0.203 in] min.
Free Position (FP)	9,53 mm [0.375 in] max.
Housing Material	Stainless Steel Bracket, Polyester Rod
Weight	41,73 g [.092 lb]
Package Height	46 mm [1.81 in]
Package Width	12,7 mm [0.50 in]
Package Length	50,0 mm [1.97 in]
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap switches
Series Name	AC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[23AC82](#)