

CATALOG LISTING

V3L-3339

M

ISSUE
2

REVISIONS

A CO-76298

JAK
11 NOV 93

REPLACES X91253-V3L

RELEASE NO. PR-19362

CHECK

CHECK

18 MAR 92

D C S

CHECK

J A L 9 MAR 92

DRAWN

DDM/CAD

MICRO SWITCH
a Honeywell Division



FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

V3L-3339

CQ-X2868




NOTES

- 1 - TERMINALS ARE SILVER PLATED FOR SOLDERING
- 2 - SWITCH MATERIAL WILL WITHSTAND TEMPERATURE OF 300°F
- 3 - HOLE IN TERMINALS MAY BREAK OUT

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE --- 150 GRAMS MAX
 RELEASE FORCE --- 15 GRAMS MIN
 DIFFERENTIAL TRAVEL --- .002-.010
 OVERTRAVEL --- .040 MIN
 RELEASE TRAVEL --- .007 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L83 15.1A 1/2HP 125, 250 VAC
 1/2A 125 VDC, 1/4A 250 VDC
 5A 125 VAC "L"



SCALE FULL

DO NOT
SCALE PRINTUNLESS OTHERWISE SPECIFIED
TOLERANCES AREONE PLACE (.0) $\pm$.030TWO PLACE (.00) $\pm$.015THREE PLACE (.000) $\pm$.005ANGLES $\pm$

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V3L-3339](#)