


**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.  
A DIVISION OF HONEYWELL


FED. MFG. CODE 91929

**SWITCH-BASIC**

CATALOG LISTING

**V3L-22****CQ-A2200**

.19 DIA X .19 WIDE OIL BRONZE ROLLER  
(CONCENTRICITY .005 T I R)



NOTE -

1- TERMINALS ARE PLATED FOR SOLDERING

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

**CHARACTERISTICS**

OPERATING FORCE — — — 14 OZ MAX

RELEASE FORCE — — — 3 OZ MIN

DIFFERENTIAL TRAVEL — — — .016 MAX

OVERTRAVEL — — — .040 MIN

RELEASE TRAVEL — — — .007 MIN

**ELECTRICAL DATA**

CONTACT ARRANGEMENT  
S P D T

L83  
15.1A 1/2HP 125 OR 250 VAC  
1/2A 125 VDC, 1/4A 250 VDC  
5A 125 VAC "L"



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE  
NOTED

DIMENSIONS ARE IN INCHES

**TOLERANCES ARE:**

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .003$
ANGLES		$\pm$

WEIGHT

**V3L-22****M**DRAWING  
NUMBER

X

X

ISSUE

4

REPLACES

SR12837

RELEASE NO.

CHECK

REVISIONS

A

C031809

RER

22 JAN 73

B

C031809

SMA

1 OCT 83

C

C031809

JAL

30 NOV 93

CHECK

SCH

CHECK

MAY 67

CHECK

MAY 67

CHECK

LSD

CHECK

MAY 67

DRAWN

M B F

5 MAY 67

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V3L-22](#)