

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY

ROSBURG, ILLINOIS

FED. MFR. CODE 91929

SWITCH-BASIC

CATALOG LISTING

V3L - 3

CQ-A0300

V3L-3

M

DRAWING
NUMBER

ISSUE
X2
X3
X4

REPLACES

RELEASE NO. SR10083

CHECK

REVISIONS

A CO 16973
GCH
16 MAY 62
B CO20189
MBF
7 SEP 65
C CO21900
LEB
14 AUG 67
D CO24941
MBS
4 DEC 68
E CO28075
MBS
27 AUG 69
F CO31509
RER
22 JAN 73
G CO 32395
GLH
14 AUG 73
H CO 36997
SMA
1 OCT 83
J CO 76445
DCS
5 JAN 94



CHECK

14 FEB 62

DRAWN

LS D

FO-30378



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ———— 14 OZ MAX
RELEASE FORCE ———— 3 OZ MIN
DIFFERENTIAL TRAVEL ———— .016 MAX
OVERTRAVEL ———— .040 MIN
RELEASE TRAVEL ———— .007 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

15.1A 1/2HP 125 OR 250 VAC
1/2A 125 VDC, 1/4A 250 VDC
5A 125 VAC "L"



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V3L-3](#)