

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

V3L-1229**CQ-P0296****V3L-1229**

PAGE 1 OF 1

MDRAWING
NUMBER

7

ISSUE

8

REPLACES

RELEASE NO. PR-5389

CHECK

REVISIONS

A

C024699

MBS

30 MAY 69

B

C026661

SRH

30 DEC 69

C

C026861

MBS

22 JAN 70

D

PR 5389

GCH

19 NOV 75

E

C0276302

JAL

30 NOV 93

F

C0284847

TSM

9 JUL 98

LSD



CHECK

MBS

25 MAR 68

DRAWN

FO-30378



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE --- 35 GRAM MAX

RELEASE FORCE --- 4 GRAM MIN

DIFFERENTIAL TRAVEL --- .030 MAX

OVERTRAVEL --- .090 MIN

RELEASE TRAVEL --- .017 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T-L112- 10A - 1/3HP - 125 OR 250 VAC
1/2A - 125 VDC: 1/4A - 250 VDC
4A - 125 VAC "L"

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V3L-1229](#)