

Manual Switches
Mounting Hardware

AML61 Series

FOR STRIP AND MATRIX MOUNT ASSEMBLIES



FEATURES

- Enables subpanel mounting of devices in factory assembled metal cans which are welded together in strips or matrices. Assures accurate alignment and enables pre-wiring.
- L-shaped mounting brackets conform to various panel thicknesses, using spacers.
- Simplifies panel fabrication, since only one large cutout is required.
- Facilitates printed circuit board mounting. Operating force is transmitted to mounting hardware, rather than P.C. board.
- For custom matrices contact the MICRO SWITCH Application Center.
- Mounting dimensions page 64.

AML61 MOUNTING HARDWARE ORDER GUIDE


(For standard strip mount assemblies)

AML61 B		A	5	A
Type	Mounting Bracket Orientation	Number of Cans	Mounting Bracket Location	
Square cans: AML61 B (Plain finish) AML61 J (Black finish)	A E	1 2 3 4 5 6 7 8 9* 10* 11* 12*	0.060 A 0.020 G BRACKET FLUSH TO TOP OF CAN 0.045 K 0.030 B 0.050 L 0.060 C 0.065 P 0.120 E 0.085 T 1.460 F U NO BRACKETS	
Rect. cans: AML61 E (Plain finish) AML61 K (Black finish)	B C D 1			

① To order one rectangular can with mounting brackets on short sides, specify AML61EB1___ or AML61KB1___.

Example: AML61EC5A

Five rectangular cans, plain finish (un-painted), long sides abutting; type A mounting brackets on long sides, located flush with switch or indicator bezel. (Type T bracket brings top of annunciator bezel flush with top of .160 in./4,1 mm panel.)



This strip has Type F brackets for P.C. board mounting.

NON-STANDARD ASSEMBLIES

Use the order form on the following page to specify non-standard AML61 strip or matrix assemblies. You may reproduce it on your office copier, or order pads from the 800 number. Request FO-63558.

Manuals

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[AML61BA1U](#) [AML61BA2A](#) [AML61BA2G](#) [AML61BA2U](#) [AML61BA3D](#) [AML61BA3U](#) [AML61BA4E](#) [AML61BA5T](#)
[AML61BA6E](#) [AML61EB1E](#) [AML61EB1U](#) [AML61EB2T](#) [AML61EB3A](#) [AML61EB4B](#) [AML61EC3A](#) [AML61EC5C](#)
[AML61EC8D](#) [AML61ED4D](#) [AML61ED6F](#) [AML61KB1E](#) [AML61KB3E](#) [AML61KB4E](#) [AML61KB5F](#) [AML61KC3E](#)
[AML61KC5E](#) [AML61EB3T](#) [AML61ED3B](#) [AML61BA1C](#) [AML61EB2C](#) [AML61EC3C](#) [AML61BA3C](#) [AML61ED2C](#)
[AML61EB1C](#) [AML61EC1C](#)