


HONEYWELL PART NUMBER
YM-1R-A2
AET1000

REV	DOCUMENT	CHANGED BY		CHECK
A	0009109	AS	02NOV04	AK
B	0010793	KRB	27JAN05	AK
C	0035411	JA	23NOV07	ASD



NOTE -
△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000±.002 CENTERS

REPLACES : X115436-YM

CHARACTERISTICS	ELECTRICAL DATA	
OPERATING FORCE-----7-10 OZ	CONTACT ARRANGEMENT S P N O	BREAK DISTANCE .010 MIN
RELEASE FORCE-----4 OZ MIN	-L161- 22 A - 125, 250, OR 480 VAC 1/8 HP - 125 VAC; 1 HP - 250 VAC L288 L315 L318 22A 250V ~ T85 5E4	
DIFFERENTIAL TRAVEL ---.0005-.0010		
OVERTRAVEL -----.005 MIN		

DESIGN UNITS: INCH	
TOLERANCES UNLESS NOTED:	
NO PLACE	X ± 0.040
ONE PLACE	.X ± 0.030
TWO PLACE	.XX ± 0.015
THREE PLACE	.XXX ± 0.005
FOUR PLACE	.XXXX ± 0.0005
ANGLES	± 2
THIRD ANGLE PROJECTION	

DRAWN	AS	02NOV04
CHECK	AK	02NOV04
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH-BASIC			
SIZE B	TYPE I	DRAWING NAME YM-1R-A2	REV C
SCALE FULL	WEIGHT : .060 LB	SHEET 1	OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[YM-1R-A2](#)