


| REV. | CHANGE | DATE | APPD. |
|------|----------------------|------|-------|
| B | REDRAWN PER ECO 8150 | — | — |



| | |
|-----------------------|--|
| EPOXY | COLOR: BLACK |
| LEADWIRES (2) | 28 AWG, 7x36 STRANDED, SILVER PLATED COPPER, BLACK TEFLON INSULATION |
| HOUSING | ALUMINUM |
| RESISTANCE | 10K OHMS AT 25°C ±0.2°C FROM 0°C TO 70°C |
| R-T CURVE | 16 |
| MAX. TEMP. | 150°C |
| INSULATION RESISTANCE | 1000 MEGOHMS MINIMUM AT 200 V.D.C. |

| | | | | | | | |
|--|---------|-------------------------|--|--|-----------|----------------------------------|-----------|
| TOLERANCES UNLESS OTHERWISE NOTED, ALL DIMENSIONS ARE IN INCHES, AND TOLERANCES ARE AS SHOWN HERE. FRACTIONS = ±1/64 DECIMALS .XX = .01 .XXX = .005 ANGLES = 0°30' | | DRAWN HS | DATE 8JUN95 | FENWAL ELECTRONICS, INC. 450 FORTUNE BOULEVARD, MILFORD, MASSACHUSETTS 01757 U.S.A. TELEPHONE (508) 478 - 6000 FAX (508) 473 - 6035 | | | |
| | | CHECKED | DATE | TITLE PROBE ASSEMBLY OUTLINE | | | |
| | | APPROVED | DATE | | | | |
| USED ON | | | This information is the property of FENWAL ELECTRONICS, INC. It is submitted in confidence, and is not to be disclosed or utilized without written permission. | | | | |
| SHEET 1 | OF 1 | DO NOT SCALE DRAWING | | SCALE 4:1 | SIZE B | DRAWING NUMBER 590-32AD05-103 | REV. B |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[590-32AD05-103](#)