

ASSEMBLY- TOGGLE SWITCH

CATALOG LISTING
31AT417-T2

31AT417-T2

M

DRAWING
NUMBER

X

8

ISSUE

8

REPLACES

RELEASE NO. PR-1478

CHECK

REVISIONS

A	CO	50566-B	WJM	10 MAY 82
B	CO	56281	GHW	28 SEP 85
C	CO	66089	DAW	27 FEB 91

CHECK

ASR

CHECK

19 OCT 70

CHECK

USD

CHECK

19 OCT 70

CHECK

SRH

7 OCT 70

CHECK

USD

CHECK

19 OCT 70

CHECK

SRH

7 OCT 70

CHECK




USD

CHECK

19 OCT 70

CHECK

SRH



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
	CONTACT ARRANGEMENT SPDT (2)	DO NOT SCALE PRINT
	250 VAC ----- 5 AMP	UNLESS OTHERWISE NOTED
	30 VOLTS DC RATING	DIMENSIONS ARE IN INCHES
	INDUCTIVE ----- SEA LEVEL ----- 3 AMP	TOLERANCES ARE:
	50,000 FT ----- 2.5 AMP	ONE PLACE (.0) ±.030
	RESISTIVE ----- SEA LEVEL ----- 5 AMP	TWO PLACE (.00) ±.015
	50,000 FT ----- 5 AMP	THREE PLACE (.000) ±.005
	MAXIMUM INRUSH ----- 24 AMP	ANGLES ±
		WEIGHT .06 LB APPROX

NOTE-

- 1 - UNIT INCLUDES CAT. LIST. 2ISM284-T2 BASIC SWITCH (2)
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - KNOB PORTION OF TOGGLE LEVER BRIGHT ANODIZED
- 4 - FOR PANEL SEAL TO BE EFFECTIVE, MTG HOLE IN PANEL SHOULD NOT EXCEED .500 DIA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[31AT417-T2](#)