







- NOTES
- 1 - UNIT INCLUDES CATALOG LISTING 21SM284-T2
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - KNOB PORTION OF TOGGLE LEVER BRIGHT ANODIZED
 - $\nabla 4$ FOR PANEL SEAL TO BE EFFECTIVE, MTG. HOLE IN PANEL SHOULD NOT EXCEED Ø.500
 - $\nabla 5$ HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET PER MIL-PRF-8805

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .06 LB APPROX

CHARACTERISTICS

ELECTRICAL DATA

CONTACT ARRANGEMENT
2X S P D T

250 VAC	-----	5 AMP
INDUCTIVE	----- SEA LEVEL -----	3 AMP
	50,000 FT -----	2.5 AMP
RESISTIVE	----- SEA LEVEL -----	5 AMP
	50,000 FT -----	5 AMP
MAXIMUM INRUSH	-----	24 AMP

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[31AT416-T2](#)