

DRAWING NUMBER	M 1TP7 SERIES CHART	
ISSUE	13	RELEASER NO
REVISIONS	A C081370 JAK 20 OCT 95 B CO-95612 JJA 1 OCT 99 C C094412 DLM 13 OCT 99	
FORMTEK	D J W 21 OCT 74	CHECK
DRAWN	14 OCT 74	CHECK
BEN	74	CHECK


MICRO SWITCH
FREERPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED MFG. CODE 9192B

**SWITCH - TOGGLE
ABOVE PANEL MOUNT**

CATALOG LISTING
1TP7 SERIES

CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH



CATALOG LISTING	CIRCUIT WITH BUTTON IN			ELECTRICAL DATA
	LUG SIDE (1-2)	CENTER (1-2)	OPPOSITE LUG (2-3)	
1TP7-1	ON	OFF	ON	L191 15A 125, 250, 277 VAC 1/2HP 125 VAC
1TP7-2	OFF	NONE	ON	1HP 250, 277 VAC 5A 125 VAC "L"
1TP7-3	ON	NONE	ON	
1TP7-21	NONE	OFF	ON	
1TP7-31	NONE	ON	ON	
1TP7-4	MOM OFF	NONE	ON	
1TP7-5	MOM ON	OFF	ON	
1TP7-6	MOM ON	NONE	OFF	
1TP7-7	MOM ON	OFF	MOM ON	
1TP7-8	MOM ON	NONE	ON	
1TP7-51	NONE	ON	MOM ON	
1TP7-61	MOM ON	OFF	NONE	

L191 15A 125, 250, 277 VAC
1/2HP 125 VAC
1HP 250, 277 VAC
5A 125 VAC "L"



L192 10A 125, 250, 277 VAC
1/4HP 125 VAC,
1/2HP 250, 277 VAC
3A 125 VAC "L"



BUTTON COLOR CODE 4

COLOR IDENTIFICATION	COLOR
W	WHITE
R	RED
Y	YELLOW
BK	BLACK
G	GREEN
BL	BLUE
T	TRANSPARENT

NOTES

1 - MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
2 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
CONTINUOUSLY AT FULL RATED LOAD

3 SCREWS FURNISHED UNASSEMBLED

4 SUFFIX MUST BE ADDED FOR DESIRED BUTTON COLOR (EXAMPLE:
1TP7-1-W)

SCALE	FULL	
DO NOT SCALE PRINT		
UNLESS OTHERWISE NOTED		
DIMENSIONS ARE IN INCHES		
TOLERANCES ARE		
ONE PLACE	±.01	±.030
TWO PLACE	±.001	±.015
THREE PLACE	±.0001	±.005
ANGLES	±10°	
WEIGHT	.09 LB EST	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell](#):

[1TP7-3](#)