

CATALOG LISTING

31AT50-T2

REPLACES

PR-22127-T

ISSUE

1

CHECK

REVISIONS

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

25

26

27

28

29

30

31

32

33

34

35

36

37

38

39

40

41

42

43

44

45

46

47

48

49

50

51

52

53

54

55

56

57

58

59

60

61

62

63

64

65

66

67

68

69

70

71

72

73

74

75

76

77

78

79

80

81

82

83

84

85

86

87

88

89

90

91

92

93

94

95

96

97

98

99

100

DDM/CAD

DRAWN

T S M





11 JUL 96

CHECK

J A F

12 JUL 96

CHECK



FLEXIBLE INSULATORS

- NOTES
- 1 - 4X UNIT INCLUDES CATALOG LISTING 1SM23-T2 TYPE GOLD CONTACT BASIC SWITCHES
  - 2 - TERMINALS ARE PLATED FOR SOLDERING
  - 3 - FOR PANEL SEAL TO BE EFFECTIVE, MOUNTING HOLE IN PANEL SHOULD NOT EXCEED Ø .500

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION
CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
	CONTACT ARRANGEMENT 4X S P D T	DO NOT SCALE PRINT
	30 VOLTS DC RATING	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
	INDUCTIVE--- SEA LEVEL--- .5 AMP 50,000 FT --- .5 AMP RESISTIVE--- SEA LEVEL--- 1 AMP 50,000 FT --- 1 AMP MAXIMUM INRUSH--- 2 AMP	ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT

ANSI Y14.5M-1982 APPLIES

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[31AT50-T2](#)