

X68280-WZ

REPLACES

PR-7685

RELEASE NO.

PA11G07

PSR

06	CHECK
----	-------

17 F

CHECK

5 FEB 76

19

CH	6279
----	------

R	T	16
---	---	----

WZ-2RW84429-P52

**DRAWING
NUMBER**


0	
1	C

REVISIONS

A	CO46220
	KAK
	30 JULY 79
B	CO51554
	TSK
	21 JULY 82
C	CO- 753678
	S A V
	3 MAR 94
D	CO- 77863
	G J W
	10 MAY 96
E	CO93346
	DLT
	22 SEP 98
F	CO018678
	TSG
	17 FEB 06
G	CO033162
	JA
	22AUG07

RASTER

O-50378



NOTE
 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
 OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ———-3/4 OZ MAX	CONTACT ARRANGEMENT	DO NOT SCALE PRINT
DIFFERENTIAL FORCE ———-1/2 OZ MAX	S P N C	UNLESS OTHERWISE SPECIFIED
PRETRAVEL ———-.625 MAX	CODE L96 15A-125, <u>250</u> OR 480 VAC	DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL ———-.027-.219	1/8 HP-125 VAC; 1/4 HP- <u>250</u> VAC	TOLERANCES ARE:
OVERTRAVEL ———-.140 MIN	1/2 A-125 VDC; 1/4 A-250 VDC	ONE PLACE (.0) ±.030
	-L288-    	TWO PLACE (.00) ±.018
	-L306- 16A 250V  T85 5E4	THREE PLACE (.000) ±.008
	-L315-	ANGLES ±
		WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[WZ-2RW84429-P52](#)