


CATALOG LISTING
YA-2RB19-A64
PAGE 1 OF 1
M
3
ISSUE
REVISIONS
A 0000683
CSL
2 JUL 03
B 0018388
TGP
17 FEB 06
CHECK
18 JUL 00
S A V
CHECK
18 JUL 00
DRAWN
DLT
18 JUL 00
RELEASE NO. 200838
REPLACES
X113024-YA



NOTE
1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF Ø.139 MAX ON 1.000±.002 CENTERS
2 COVER BONDED TO SWITCH CASE

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		THIRD ANGLE PROJECTION	
CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE----- 14-22 OZ	CONTACT ARRANGEMENT	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE----- 10 OZ MIN	SP NO	ONE PLACE (.0)	±.030
DIFFERENTIAL TRAVEL----- .002-.0075	L23 20A 125, 250 OR 480 VAC	TWO PLACE (.00)	±.015
OVERTRAVEL----- .094 MIN	10A 125 VAC "L"	THREE PLACE (.000)	±.005
	1HP 125 VAC, 2HP 250 VAC	ANGLES	±
	1/2A 125 VDC, 1/4A 250 VDC	WEIGHT	.064 LB
	L288 L308 L315		
	20(3)A 250V T85 5E4		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[YA-2RB19-A64](#)